# **Product data sheet**

Specifications



## Power Cord, C19 to C20, 4.5m

AP9887



#### **Overview** Presentation Rack PDU power cords for a variety of IT equipment. The output and input connections are C19 to C20. The cord length is 4.5m. The Nominal Output Voltage is 230V. Lead Time Usually in Stock Main Main Output Voltage 230 V Input Connection Type IEC 60320 C20 Cable Length 4.57 m Number Of Cables 1 Physical Colour Black Net Weight 1.59 kg **Mounting Preference** No preference Mounting Mode Not rack-mountable Input Permissible Voltage 200...240 V Input Current Limits 16 A Output Max Current Draw 16 A Number Of Power Socket Outlets 1 IEC 60320 C19

#### Conformance

Product Certifications

VDE

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	57.2 cm
Package 1 Width	11.4 cm
Package 1 Length	47 cm



Package 1 Weight

1.82 kg

#### **Contractual warranty**

Warranty

2 years repair or replace

### Sustainability

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.





#### **Resource performance**

Take-Back Program Available

#### Well-being performance

Lead Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information



