

Product data sheet

Specifications



3-Pole Circuit Breaker, 100A, T1 Type for Symmetra PX250/500kW

PD3P100AT1B

Overview

Lead time Special Order - Call for Quoted Lead Times

Main

Main Input Voltage 480 V 3 phases
400 V 3 phases

Main Output Voltage 480 V 3 phases
400 V 3 phases

Output connector type Hard wire 3-wire (3P) 1

Provided equipment Installation guide

Physical

Height 43.2 cm

Width 55.9 cm

Depth 54.6 cm

Net weight 1.86 kg

Mounting location Front

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Max line current 100 A

Network frequency 50 Hz
60 Hz

Output

Max current draw 100 A

Conformance

Product certifications CE
UL listed

Environmental

Ambient air temperature for operation 0...40 °C

Ambient air temperature for storage -15...40 °C

Packing Units

Package 1 Weight 2.8 kg

Package 1 Height 43.2 cm

Package 1 width 55.9 cm

Package 1 Length 54.6 cm

Offer Sustainability

EU RoHS Directive Under investigation

Contractual warranty

Warranty 1 year repair or replace