

Product data sheet

Specifications



Adaptor for T1 Type Circuit Breaker, 3 Pole

PD3PADAPT1

Overview

Lead Time Usually Ships within 6 Weeks

Main

Main Input Voltage 480 V 3 phases
400 V 3 phases

Output Connector Type Hard wire 3-wire (3P) 1

Provided Equipment Installation guide

Physical

Height 15.2 cm

Width 10.2 cm

Depth 7.6 cm

Net Weight 1.14 kg

Mounting Location Front

Mounting Preference No preference

Mounting Mode Not rack-mountable

Input

Network Frequency 50 Hz
60 Hz

Output

Max Current Draw 400 A

Conformance

Product Certifications CE
CSA
UL listed

Environmental

Ambient Air Temperature For Operation 0...40 °C

Ambient Air Temperature For Storage -15...40 °C

Packing Units

Unit Type Of Package 1 PCE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	46.7 cm
Package 1 Width	19.4 cm
Package 1 Length	25.9 cm
Package 1 Weight	1.36 kg

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)

Eu Rohs Directive

Under investigation