

Product data sheet

Specifications

APC SERVICE BYPASS PDU, 230V 16AMP Hardwire



SBP3000RMHW

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Main Output Voltage 230 V

Output connector type Hard wire 3-wire (H N + E) 1

Number of rack unit 2U

Provided equipment User manual
Rack mounting brackets

Physical

Colour Black

Height 8.9 cm

Width 43.2 cm

Depth 7.6 cm

Net weight 2.27 kg

Mounting location Front

Mounting preference No preference

Mounting mode Rack-mounted

Input

Network frequency 50/60 Hz

Permissible voltage 220...240 V

Max line current 16 A

Input current limits 16 A

Load capacity 3000 VA

Power factor 0...1

Output

Max current draw 16 A

Number of power socket outlets 1 IEC Jumpers

Protection type	Circuit breaker
Power cable length	1.00 m
Efficiency	99 %

Conformance

Product certifications	VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Height	15.1 cm
Package 1 Width	46.3 cm
Package 1 Length	29.5 cm
Package 1 Weight	3.45 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	64
Package 2 Height	135 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	225.28 kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)