

Product data sheet

Specifications



APC Smart-UPS RT Battery Pack 48V

SURT48XLBP

Overview

Lead time Usually in Stock

Main

Number of rack unit 2U
Number of cables 1
Battery type Lead-acid battery
Provided equipment Installation guide
User manual

Physical

Colour Black
Height 8.5 cm
Width 43.2 cm
Depth 48.3 cm
Net weight 29.56 kg
Mounting preference No preference
Mounting mode Not rack-mountable
Two post mountable 0
USB compatible No

Output

Harmonic distortion Less than 3 %
Output frequency 50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains
Crest factor 3 : 1
Wave type Sine wave
Bypass type Built-in static bypass


Environmental

Ambient air temperature for operation 0...40 °C
Relative humidity 0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Batteries & Runtime

Number of battery filled slots	2
Number of battery free slots	0
Number of battery replacement quantity	2
Additional information	Replace all batteries in operation together (UPS internal and external batteries) all-at-once
Replacement battery	RBC31 

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28.6 cm
Package 1 Width	63 cm
Package 1 Length	59.4 cm
Package 1 Weight	32.28 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	135 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	420 kg

Contractual warranty

Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
----------	--

Recommended replacement(s)