



APC High Performance Battery Module for the Symmetra PX 250/500kW

SYBT9-B6

Overview

Lead Time Usually in Stock

Main

Battery Type	VRLA
Provided Equipment	Installation guide

Batteries & Runtime

Battery Location	Internal battery
Number Of Battery Blocks Per String	6
Battery Life	35 year(s)
Device Mounting	Enclosed battery cartridge
Battery Voltage	384 V
Battery Power In Vah	5184 VAh

Physical

Height	15.9 cm
Width	10.7 cm
Depth	70 cm
Net Weight	153 kg

Conformance

Product Certifications	cUL listed	
	EUROBAT	
	UL listed	
	VDE	

Environmental

Ambient Air Temperature For Operation	1827 °C
Operating Altitude	03333 ft
Relative Humidity	095 %
Ambient Air Temperature For Storage	-1540 °C
Storage Altitude	0.0015240.00 m
Storage Relative Humidity	095 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18 cm
Package 1 Width	81 cm
Package 1 Length	64.8 cm
Package 1 Weight	160.91 kg

Contractual warranty

Warranty 1 year (parts only)



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile