

Product datasheet

Specifications



RACK PDU, BASIC, 0U/1U, 120-240V/15A, 220-240V/10A, (8) C13

AP6015A

Overview

Lead time Usually in Stock

Main

Main Input Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Main Output Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Input Connection Type IEC 60320 C14

Number of rack unit 1U

Provided equipment Installation guide
Safety guide

Physical

Colour Black

Height 24 cm

Width 4.4 cm

Depth 9.3 cm

Net weight 0.91 kg

Mounting location Front
Rear

Mounting preference No preference

Mounting mode Not rack-mountable

Input

[In] rated current 12 A

Permissible voltage 100...240 V

Max line current 15 A

Input current limits 15 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Load capacity	2300 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

Conformance

Product certifications	cUL listed CE EAC IRAM UL listed VDE
------------------------	---

Packing Units

Package 1 Weight	1.37 kg
Package 1 Height	28.6 cm
Package 1 width	21 cm
Package 1 Length	13 cm
SCC14	10731304327797
Number of Units in Package 3	192

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------