# **Product datasheet**

Specifications



#### Overview

Lead Time

Usually in Stock

#### Main

| Colour             | Black                                 |
|--------------------|---------------------------------------|
| Pdu Type           | Basic                                 |
| Cord Length        | 2.50 m                                |
| Number Of Cables   | 1                                     |
| Provided Equipment | User manual<br>Rack mounting brackets |

### Complementary

| <b>Complemental J</b>   |                  |  |
|-------------------------|------------------|--|
| Input Voltage           | 120 V            |  |
|                         | 208 V            |  |
|                         | 230 V            |  |
|                         | 230 V            |  |
| Height                  | 4.4 cm           |  |
| Width                   | 44.7 cm          |  |
| Output Voltage          | 120 V            |  |
|                         | 208 V            |  |
|                         | 230 V            |  |
| Depth                   | 5.7 cm           |  |
| Net Weight              | 0.98 kg          |  |
| Mounting Location       | Front            |  |
|                         | Rear             |  |
| Mounting Preference     | No preference    |  |
| Input Plug Type         | IEC 60320 C20    |  |
| Mounting Mode           | Rack-mounted     |  |
| Rack Units              | 1U               |  |
| Mounting Position       | Horizontal       |  |
| Permissible Voltage     | 90250 V          |  |
| Max Line Current        | 16 A             |  |
| Input Current Limits    | 16 A             |  |
| Load Capacity           | 3680 VA          |  |
| Network Frequency       | 50/60 Hz         |  |
| Total Number Of Outlets | 10 IEC 60320 C13 |  |
|                         | 2 IEC 60320 C19  |  |
|                         |                  |  |



## Environment

| Product Certifications                   | cUL listed<br>CE<br>UL listed<br>VDE<br>Victoria |
|--|--|
| Ambient Air Temperature For<br>Operation | 045 °C   |
| Relative Humidity                        | 095 %  |
| Operating Altitude                       | 010000 ft  |
| Ambient Air Temperature For<br>Storage   | -2565 °C   |
| Storage Relative Humidity                | 095 %  |
| Storage Altitude                         | 0.0015240.00 m                                   |

# **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 16.5 cm  |
| Package 1 Width              | 48.3 cm  |
| Package 1 Length             | 15.2 cm  |
| Package 1 Weight             | 2.355 kg |

## **Contractual warranty**

Warranty

2 years repair or replace

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



Energy Efficient Take-back Transparency RoHS/REACh

#### **Resource performance**

Energy Efficient Product

Take-Back Program Available

#### Well-being performance

Lead Free

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant<br>EU RoHS Declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |

