

# Product datasheet

Specifications

## EasyPDU, Metered-by-Outlet with Switching, ZeroU, 16A, 230V, (20) C13 & (4) C19



EPDU1116SMBO

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60309 16 A 2P + E
Number of rack unit	0U
Cable length	3 m
Number of cables	1
Communication port protocol	SNMP
Provided equipment	Installation guide Safety guide Rack mounting brackets

### Physical

Colour	Black
Height	1800 mm
Width	55 mm
Depth	56 mm
Net weight	6.67 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Not rack-mountable
USB compatible	No
Mounting position	Vertical

### Input

[In] rated current	16 A
Permissible voltage	200...240 V
Max line current	16 A

Input current limits	16 A
Load capacity	3680 VA
Network frequency	50/60 Hz
Plug standard	IEC 60309

## Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

## Conformance

Product certifications	CE EAC TÜV RCM UKCA
------------------------	---------------------------------

## Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...3000 m
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0...15000 mm

## Batteries & Runtime

Communication network type	10/100BASE-T
----------------------------	--------------

## Packing Units

Number of Units in Package 1	1
Package 1 Weight	7.84 kg
Package 1 Height	2030 mm
Package 1 width	195 mm
Package 1 Length	130 mm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------