

Product datasheet

Specifications



Easy PDU, Basic, Zero U, 11 kW, 230V, (36) C13 & (6) C19 ; IEC309

EPDU1216B

Overview

Lead time Usually in Stock

Main

Main Input Voltage 400 V 3 phases

Main Output Voltage 230 V

Input Connection Type IEC 60309 16 A 3P + N + PE

Number of rack unit 0U

Cable length 1.98 m

Number of cables 1

Physical

Colour Black

Height 150.6 cm

Width 6.2 cm

Depth 4.44 cm

Net weight 3.08 kg

Mounting location Side

Mounting preference No preference

Mounting mode Rack-mounted

Input

Input current limits 16 A

Load capacity 11000 VA

Network frequency 50/60 Hz

Output

Number of power socket outlets 36 IEC 60320 C13
6 IEC 60320 C19

Conformance

Product certifications CE
TÜV

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	4.28 kg
Package 1 Height	166 cm
Package 1 width	16 cm
Package 1 Length	11 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------