

Product datasheet

Specifications

Easy PDU, Metered, Zero U, 11 kW, 230V, (21) C13 & (3) C19;IEC309



EPDU1216M

Overview

Lead time Usually in Stock

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V
Input Connection Type	IEC 60309 16 A 3P + N + PE
Number of rack unit	0U
Cable length	1.98 m
Number of cables	1
Provided equipment	Installation guide Toolless mounting kit Vertical mounting brackets

Physical

Colour	Black
Height	117.5 cm
Width	6.2 cm
Depth	4.44 cm
Net weight	2.74 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Input current limits	16 A
Load capacity	11000 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product certifications	CE EAC RCM TÜV
------------------------	-------------------------

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-20...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...4572.00 m

Packing Units

Package 1 Weight	3.26 kg
Package 1 Height	132 cm
Package 1 width	16 cm
Package 1 Length	11 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------