

Product datasheet

Specifications



Rack PDU, Basic, Zero U, 32A, 230V, (20)C13 & (4)C19

AP7553

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
PDU type	Basic
Main Output Voltage	230 V
Input Connection Type	IEC 60309 32 A 2P + E
Number of rack unit	0U
Cable length	3.05 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets Toolless mounting kit

Physical

Colour	Black
Height	161.9 cm
Width	5.6 cm
Depth	4.4 cm
Net weight	5.57 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Input current limits	32 A
Load capacity	7400 VA
Network frequency	47...63 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product certifications	CE VDE
------------------------	-----------

Environmental

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	212.1 cm
Package 1 Width	15.2 cm
Package 1 Length	12.7 cm
Package 1 Weight	6.466 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)