

# Product datasheet

Specifications



## Rack PDU, Basic, ZeroU, 16A, 230V, (20)C13 & (4)C19; IEC309, 10 ft Cord

AP7554

### Overview

Lead time Usually in Stock

### Main

|                       |   |
|-----------------------|---|
| Main Input Voltage    | 200 V<br>208 V<br>230 V   |
| PDU type              | Basic   |
| Main Output Voltage   | 230 V   |
| Input Connection Type | IEC 60309 16 A  |
| Number of rack unit   | 0U  |
| Cable length          | 3.05 m  |
| Number of cables      | 1   |
| Provided equipment    | Installation guide<br>Rack mounting brackets<br>Toolless mounting kit |

### Physical

|                     |               |
|---------------------|---------------|
| Colour              | Black         |
| Height              | 161.9 cm      |
| Width               | 5.6 cm        |
| Depth               | 4.4 cm        |
| Net weight          | 5.57 kg       |
| Mounting location   | Side          |
| Mounting preference | No preference |
| Mounting mode       | Rack-mounted  |

### Input

|                      |            |
|----------------------|------------|
| Input current limits | 16 A       |
| Load capacity        | 3680 VA    |
| Network frequency    | 47...63 Hz |

## Output

|                                |                                     |
|--------------------------------|-------------------------------------|
| Number of power socket outlets | 20 IEC 60320 C13<br>4 IEC 60320 C19 |
|--------------------------------|-------------------------------------|

## Conformance

|                        |           |
|------------------------|-----------|
| Product certifications | CE<br>VDE |
|------------------------|-----------|

## Environmental

|                                       |            |
|---------------------------------------|------------|
| Ambient air temperature for operation | -5...45 °C |
|---------------------------------------|------------|

|                   |          |
|-------------------|----------|
| Relative humidity | 5...95 % |
|-------------------|----------|

|                    |              |
|--------------------|--------------|
| Operating altitude | 0...10000 ft |
|--------------------|--------------|

|                                     |             |
|-------------------------------------|-------------|
| Ambient air temperature for storage | -25...65 °C |
|-------------------------------------|-------------|

|                           |          |
|---------------------------|----------|
| Storage Relative Humidity | 5...95 % |
|---------------------------|----------|

|                  |                   |
|------------------|-------------------|
| Storage altitude | 0.00...15240.00 m |
|------------------|-------------------|

## Packing Units

|                        |    |
|------------------------|----|
| Unit Type of Package 1 | Db |
|------------------------|----|

|                              |   |
|------------------------------|---|
| Number of Units in Package 1 | 1 |
|------------------------------|---|

|                  |          |
|------------------|----------|
| Package 1 Height | 213.4 cm |
|------------------|----------|

|                 |         |
|-----------------|---------|
| Package 1 Width | 15.2 cm |
|-----------------|---------|

|                  |         |
|------------------|---------|
| Package 1 Length | 12.7 cm |
|------------------|---------|

|                  |          |
|------------------|----------|
| Package 1 Weight | 6.466 kg |
|------------------|----------|

## Offer Sustainability

|                          |                       |
|--------------------------|-----------------------|
| Sustainable offer status | Green Premium product |
|--------------------------|-----------------------|

|                  |                                   |
|------------------|-----------------------------------|
| REACH Regulation | <a href="#">REACH Declaration</a> |
|------------------|-----------------------------------|

|                   |  |
|-------------------|--|
| EU RoHS Directive | Compliant<br><a href="#">EU RoHS Declaration</a> |
|-------------------|--|

|           |     |
|-----------|-----|
| Lead free | Yes |
|-----------|-----|

|      |   |
|------|---|
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
|------|---|

|                             |                          |
|-----------------------------|--------------------------|
| Optimized Energy Efficiency | Energy efficient product |
|-----------------------------|--------------------------|

|           |                             |
|-----------|-----------------------------|
| Take-back | Take-back program available |
|-----------|-----------------------------|

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

## Recommended replacement(s)