

# Product datasheet

Specifications



## APC NetShelter Switched Rack PDU, 1U, 1PH, 3.7kW 230V 16A or 3.3kW 208V 16A, x8 C13 outlets, C20 cord

AP7921B

### Overview

**Presentation** This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.

**Lead time** Usually in Stock

### Main

<b>Main Input Voltage</b>	200 V 208 V 230 V
<b>PDU type</b>	Switched
<b>Main Output Voltage</b>	208 V 230 V
<b>Input Connection Type</b>	IEC 60320 C20
<b>Number of rack unit</b>	1U
<b>Cable length</b>	2.50 m
<b>Number of cables</b>	1
<b>Provided equipment</b>	Installation guide Rack mounting brackets User manual

### Physical

<b>Colour</b>	Black
<b>Height</b>	4.4 cm
<b>Width</b>	44.5 cm
<b>Depth</b>	10.8 cm
<b>Net weight</b>	2.27 kg
<b>Mounting location</b>	Front Rear
<b>Mounting preference</b>	No preference
<b>Mounting mode</b>	Rack-mounted

## Input

[In] rated current	16 A
Permissible voltage	200...240 V
Input current limits	20 A
Load capacity	3680 VA
Network frequency	50/60 Hz

## Output

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

## Conformance

Product certifications	cUL listed CE CSA GOST IRAM MIC UL listed VDE VCCI
------------------------	--

Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
-----------	--

## Environmental

Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	34.3 cm
Package 1 Length	47 cm
Package 1 Weight	3.45 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

<b>Circularity Profile</b>	<a href="#">End of Life Information</a>
<b>Optimized Energy Efficiency</b>	Energy efficient product
<b>Take-back</b>	Take-back program available

---

## **Contractual warranty**

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## **Recommended replacement(s)**