

Product datasheet

Specifications



APC Replacement Battery Cartridge #48 with 2 Year Warranty

RBC48

Overview

Lead time Usually in Stock

Main

Battery type Lead-acid battery

Provided equipment All required connectors
Battery recycling guide
Reusable packaging
Installation guide

Physical

Height 10.8 cm

Width 13.2 cm

Depth 15 cm

Net weight 5 kg

Mounting mode Not rack-mountable

USB compatible No

Output

Battery capacity 7.0 Ah

Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 %

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

Batteries & Runtime

Number of battery blocks per string 2

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Stand alone battery stack
Battery voltage	24 V
Number of battery replacement quantity	1

Packing Units

Package 1 Weight	5.91 kg
Package 1 Height	16.8 cm
Package 1 width	16.8 cm
Package 1 Length	22.4 cm
Number of Units in Package 3	75

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------