

Product datasheet

Specifications



RACK PDU, BASIC, HALF HEIGHT, 100-240V/20A, 220-240V/16A, (14) C13

AP6003A

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Main Output Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Input Connection Type IEC 60320 C20

Number of rack unit 0U

Provided equipment Installation guide
Safety guide

Physical

Colour Black

Height 52.3 cm

Width 5.6 cm

Depth 4.7 cm

Net weight 1.88 kg

Mounting location Side

Mounting preference Lower

Mounting mode Not rack-mountable

USB compatible No

Input

[In] rated current 16 A

Permissible voltage 100...240 V

Max line current 20 A

Input current limits 20 A

Load capacity 3300 VA

Network frequency 50/60 Hz

Output

Number of power socket outlets	14 IEC 60320 C13
--------------------------------	------------------

Conformance

Product certifications	cUL listed UL listed
------------------------	-------------------------

Environmental

Ambient air temperature for operation	0...50 °C
---------------------------------------	-----------

Relative humidity	5...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-15...65 °C
-------------------------------------	-------------

Storage Relative Humidity	5...95 %
---------------------------	----------

Storage altitude	0.00...15240.00 m
------------------	-------------------

Packing Units

Package 1 Weight	2.55 kg
------------------	---------

Package 1 Height	61.2 cm
------------------	---------

Package 1 width	12.3 cm
-----------------	---------

Package 1 Length	10.7 cm
------------------	---------

SCC14	10731304327766
-------	----------------

Number of Units in Package 3	96
------------------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Lead free	Yes
-----------	-----

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Take-back	Take-back program available
-----------	-----------------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------