

# Product datasheet

Specifications



## Rack PDU, Switched, Zero U, 10A, 230V, (16) C13

AP7950B

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Colour	Black
Pdu Type	Switched
Cord Length	3.05 m
Number Of Cables	1
Provided Equipment	Cord retention bracket(s) Installation guide Rack mounting brackets Toolless mounting kit User manual

### Complementary

Input Voltage	200 V 208 V 230 V
Height	124.5 cm
Width	5.6 cm
Output Voltage	230 V
Depth	4.4 cm
Net Weight	4.32 kg
Mounting Location	Rear
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	0U
Mounting Position	Vertical
Permissible Voltage	200...240 V
Max Line Current	10 A
Input Current Limits	10 A
Load Capacity	2300 VA
Network Frequency	47...63 Hz
Total Number Of Outlets	16 IEC 60320 C13

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Product Certifications	CE GOST IRAM VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3
Ambient Air Temperature For Operation	-5...45 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.4 cm
Package 1 Width	12.7 cm
Package 1 Length	15.2 cm
Package 1 Weight	5.23 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



Energy Efficient   Take-back   Transparency   RoHS/REACH

Resource performance

- ✓

 Energy Efficient Product
- ✓

 Take-Back Program Available

Well-being performance

- ✓

 Lead Free
- ✓

 Mercury Free
- ✓

 Rohs Exemption Information   [Yes](#)

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>