

# Product datasheet

Specifications



## APC Replacement Battery Cartridge #113 with 2 Year Warranty

APCRBC113

### Overview

Lead time Usually in Stock

### Main

Product or component type Replacement battery cartridge

Battery type Lead-acid battery

Provided equipment All required connectors  
Battery recycling guide  
Installation guide  
Reusable packaging

### Physical

Colour Black

Height 10.2 cm

Width 13.3 cm

Depth 15.2 cm

Net weight 6.8 kg

Mounting mode Not rack-mountable

### Output

Battery capacity 7.0 Ah

### Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 %

Ambient air temperature for storage -5...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

### Batteries & Runtime

Number of battery free slots 0

|  |                            |
|--|----------------------------|
| Number of battery filled slots         | 0                          |
| Device mounting                        | Enclosed battery cartridge |
| Battery voltage                        | 24 V                       |
| Number of battery replacement quantity | 1                          |

## Packing Units

|                              |                |
|------------------------------|----------------|
| Unit Type of Package 1       | PCE            |
| Number of Units in Package 1 | 1              |
| Package 1 Height             | 14 cm          |
| Package 1 Width              | 17.1 cm        |
| Package 1 Length             | 21 cm          |
| Package 1 Weight             | 7 kg           |
| SCC14                        | 10731304260049 |

## Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| REACH Regulation         | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | <a href="#">End of Life Information</a>   |
| Take-back                | Take-back program available   |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

## Recommended replacement(s)