

# Product datasheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 45U, Black, 2124H x 600W x 1200D mm

AR3305

### Overview

Presentation	An industry-standard server rack ready for medium to high-density environments with traditional network closet 2&4 post rack height and 3U extra space. A deeper rack design provides enough rack mounting space for even the deepest devices and still plenty of room for vertically mounting Rack PDUs and cable management.
Lead Time	Usually in Stock

### Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	45U
Provided Equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

### Physical

Height	212.4 cm
Width	60 cm
Depth	120 cm
Net Weight	141 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	104.8 cm
Minimum Mounting Depth	19.05 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	1020.58 kg dynamic 1700.97 kg static

### Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	224 cm
Package 1 Width	133.4 cm
Package 1 Length	74.6 cm
Package 1 Weight	158.4 kg

## Contractual warranty


Warranty	5 year repair or replace
----------	--------------------------


Sustainability




**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)







Take-back

Transparency

RoHS/REACH

Resource performance




Take-Back Program Available

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>