Product datasheet

Specifications





APC Smart-UPS On-Line SRT Battery Pack for 8/10kVA Extended runtime model 192V

SRT192BP2

Overview

Lead Time

Usually in Stock

Main

Battery Type	Lead-acid battery
Provided Equipment	Documentation CD Installation guide Warranty card

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Stand alone battery stack
Battery Voltage	+/- 192 V
Number Of Battery Replacement Quantity	2
Replacement Battery	APCRBC140

Physical

•	
Colour	Black
Height	43.2 cm
Width	13 cm
Depth	68.27 cm
Net Weight	91 kg
Mounting Mode	Rack-mounted with kit

Environmental

Ambient Air Temperature For Operation	040 °C
Operating Altitude	010000 ft
Relative Humidity	095 % non-condensing
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Storage Relative Humidity	095 % non-condensing

Packing Units



Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	42 cm
Package 1 Width	60 cm
Package 1 Length	100 cm
Package 1 Weight	101.5 kg

Contractual warranty

Warranty

2 years repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.





Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

