

# Product datasheet

Specifications



## APC Smart-UPS SRT 192V 8kVA and 10kVA Battery Pack

SRT192BP2

### Overview

Lead time Usually in Stock

### Main

Battery type Lead-acid battery

Provided equipment Documentation CD  
Installation guide  
Warranty card

### Physical

Colour Black

Height 43.2 cm

Width 13 cm

Depth 68.27 cm

Net weight 91 kg

Mounting mode Rack-mounted with kit

### Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 % non-condensing

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity Non-condensing 0...95 %

### Batteries & Runtime

Number of battery free slots 0

Number of battery filled slots 0

Device mounting Stand alone battery stack

Battery voltage +/- 192 V

Number of battery replacement quantity 2

---

Replacement battery [APCRBC140](#) 

## Packing Units

---

Package 1 Weight 101.5 kg

---

Package 1 Height 42 cm

---

Package 1 width 60 cm

---

Package 1 Length 100 cm

---

Number of Units in Package 3 1

## Offer Sustainability

---

Sustainable offer status Green Premium product

---

REACH Regulation [REACH Declaration](#)

---

EU RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

---

Environmental Disclosure [Product Environmental Profile](#)

---

Circularity Profile [End of Life Information](#)

---

Take-back Take-back program available

## Contractual warranty

---

Warranty 2 years repair or replace