

Product data sheet

Specifications



MGE SNMP/Web Card

66074

Overview

Lead time Usually in Stock

Main

Provided Equipment User Manual

Physical

Color Gray

Height 1.10 in (2.8 cm)

Width 3.90 in (9.9 cm)

Depth 5.71 in (14.5 cm)

Net Weight 0.66 lb(US) (0.3 kg)

Mounting preference No preference

Mounting Mode Not rack-mountable

Conformance

Standards EN 60950
EN 61000-3-2

Environmental

Ambient Air Temperature for Operation 23...113 °F (-5...45 °C)

Relative Humidity 0...95 %

Operating altitude 0...10000 ft

Ambient Air Temperature for Storage 14...140 °F (-10...60 °C)

Storage Relative Humidity 0...95 %

Storage altitude 0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN 731304300229

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	6.30 in (16 cm)
Package 1 Length	9.25 in (23.5 cm)
Package 1 Weight	1.10 lb(US) (0.5 kg)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)