

Product data sheet

Specifications



UPS Communications Cable Smart Signalling

940-0024

Overview

Lead time Usually in Stock

Main

Cable length 6.56 ft (2.00 m)

Number of cables 1

Product Compatibility UPS

Physical

Color Black

Net Weight 1.01 lb(US) (0.46 kg)

Mounting Location Front

Mounting Mode Not rack-mountable

Connector B SUB-D 9 male Smart Signaling

Connector A SUB-D 9 female Smart Signaling

Output

Number of port 1

Environmental

Storage Relative Humidity 0...95 %

Storage altitude 0...50000 ft (0.00...15240.00 m)

Ambient Air Temperature for Operation 32...113 °F (0...45 °C)

Relative Humidity 0...95 %

Operating altitude 0...10000 ft

Ambient Air Temperature for Storage 5...113 °F (-15...45 °C)

Ordering and shipping details

GTIN 731304316350

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.02 in (22.9 cm)
Package 1 Width	2.01 in (5.1 cm)
Package 1 Length	4.02 in (10.2 cm)
Package 1 Weight	1.01 lb(US) (0.46 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)