

Product data sheet

Specifications

Rack PDU, Switched, 1U, 12A/208V, 10A/230V, (8)C13



AP7920

! Discontinued on: 23 August 2021

! End-of-service on: 08 October 2021

! Discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V 230 V
Input Connection Type	IEC 60320 C14
Number of rack unit	1U
Cable length	6.5 ft (1.98 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.52 in (44.5 cm)
Depth	4.25 in (10.8 cm)
Net Weight	5.00 lb(US) (2.27 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	12 A
Acceptable Input Voltage	200...240 V
Input current limits	15 A
Load Capacity	2300 VA

Input Frequency	50/60 Hz
-----------------	----------

Output

Different voltages and corresponding amperages	10 A - 230 V 12 A - 208 V
--	------------------------------

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

Conformance

Product Certifications	cUL Listed CE CSA GOST IRAM UL Listed VDE
------------------------	---

Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
-----------	--

Environmental

Ambient air temperature for operation	32...113 °F (0...45 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
-------------------------------------	----------------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0...50000 ft (0.00...15240.00 m)
------------------	----------------------------------

Ordering and shipping details

GTIN	731304210801
------	--------------

Package weight(Lbs)	7.61 lb(US) (3.45 kg)
---------------------	-----------------------

Packing Units

Package 1 Height	2.76 in (7 cm)
------------------	----------------

Package 1 width	18.50 in (47 cm)
-----------------	------------------

Package 1 Length	13.50 in (34.3 cm)
------------------	--------------------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
-------------------	--

Mercury free	Yes
--------------	-----

RoHS exemption information	Yes
----------------------------	---------------------

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
------	--

Optimized Energy Efficiency	Energy efficient product
-----------------------------	--------------------------

Take-back	Take-back program available
-----------	-----------------------------

Contractual warranty

Warranty

2 years repair or replace

Recommended replacement(s)

AP7920 is replaced by:

1x



Rack PDU, Switched, 1U, 12A/208V, 10A/230V, (8)C13

AP7920B
