

Product data sheet

Specifications



APC NetShelter Switched Rack PDU, 1U, 1PH , 2.3kW 230V 10A or 2.5kW 208V 12A, x8 C13 outlets, C14 cord

AP7920B

Overview

Presentation This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.

Lead time Usually in Stock

Main

Main Input Voltage 200 V
208 V
230 V

Main Output Voltage 208 V
230 V

Input Connection Type IEC 60320 C14

Number of rack unit 1U

Cable length 6.5 ft (1.98 m)

Number of cables 1

Provided Equipment Installation guide
Rack Mounting brackets
User Manual

Physical

Color Black

Height 1.73 in (4.4 cm)

Width 17.52 in (44.5 cm)

Depth 4.25 in (10.8 cm)

Net Weight 5.00 lb(US) (2.27 kg)

Mounting Location Front
Rear

Mounting preference No preference

Mounting Mode Rack-mounted

Input

Line Rated Current 12 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Acceptable Input Voltage	200...240 V
Input current limits	15 A
Load Capacity	2300 VA
Input Frequency	50/60 Hz

Output

Different voltages and corresponding amperages	10 A - 230 V 12 A - 208 V
Number of power socket outlets	8 IEC 60320 C13

Conformance

Product Certifications	cUL Listed CE CSA GOST IRAM UL Listed VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304331612
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	13.50 in (34.3 cm)
Package 1 Length	18.50 in (47 cm)
Package 1 Weight	7.61 lb(US) (3.45 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Recommended replacement(s)