Product data sheet

Specification





APC NetShelter Switched Rack PDU, 1U, 1PH, 2.3kW 230V 10A or 2.5kW 208V 12A, 8 C13 outlets, C14 cord

AP7920B

Overview

Presentation	This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)C13. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.
Lead Time	Usually in Stock

Main

Color	Black
Pdu Type	Switched
Cord Length	6.5 ft (1.98 m)
Number Of Cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Complementary

Input Voltage	200 V
	208 V
	230 V
Height	1.73 in (4.4 cm)
Width	17.52 in (44.5 cm)
Output Voltage	208 V
	230 V
Depth	4.25 in (10.8 cm)
Net Weight	5.00 lb(US) (2.27 kg)
Mounting Location	Front
	Rear
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	1U
Mounting Position	Horizontal
Line Rated Current	12 A

Acceptable Input Voltage	200240 V
Input Current Limits	15 A
Load Capacity	2300 VA
Different Voltages And Corresponding Amperages	10 A - 230 V 12 A - 208 V
Input Frequency	50/60 Hz
Outlet Type And Quantity	8 IEC 60320 C13

Environment

Product Certifications	cUL Listed CE CSA GOST IRAM UL Listed VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 UL 60950
Ambient Air Temperature For Operation	32113 °F (045 °C)
Relative Humidity	095 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	095 %
Storage Altitude	050000 ft (0.0015240.00 m)

Ordering and shipping details

Gtin 731304331612

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	13.50 in (34.3 cm)
Package 1 Length	18.50 in (47 cm)
Package 1 Weight	7.61 lb(US) (3.45 kg)

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product



Take-Back Program Available

Well-being performance

Mercury Free

Reach Regulation



Rohs Exemption Information

Certifications & Standards

REACh Declaration Eu Rohs Directive Compliant with Exemptions **Environmental Disclosure Product Environmental Profile Circularity Profile** End of Life Information WARNING: This product can expose you to chemicals including: Diisononyl California Proposition 65 phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov