

Product data sheet

Specifications



APC Temperature & Humidity Sensor

AP9335TH



Overview

Presentation	This Temperature & Humidity Sensor is a Universal sensor that monitors temperature and humidity in your Data Center or Network Closet. IT has an RJ-45 connector. The cord length is 3.9m.
Lead time	Usually in Stock

Main

Number of rack unit	0U
Provided Equipment	Humidity sensor Installation guide Temperature Sensor

Physical

Color	Black
Height	0.24 in (0.6 cm)
Width	0.20 in (0.5 cm)
Depth	0.20 in (0.5 cm)
Net Weight	0.40 lb(US) (0.18 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

Environmental

Ambient air temperature for operation	32...131 °F (0...55 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Ordering and shipping details

Category	09305 - INDUSTRIAL UPS
GTIN	731304234005
Nbr. of units in pkg.	1

Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	0.39 in (1 cm)
Package 1 width	10.00 in (25.4 cm)
Package 1 Length	5.98 in (15.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------