# **Product data sheet**



Input Current Limits



15 A

Load Capacity	1400 VA
Input Frequency	50/60 Hz
Total Number Of Outlets	14 NEMA 5-15R

### Environment

Product Certifications	cUL Listed METI Denan UL Listed
Ambient Air Temperature For Operation	32113 °F (045 °C)
Relative Humidity	095 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	095 %
Storage Altitude	050000 ft (0.0015240.00 m)

# Ordering and shipping details

Gtin

731304207061

### **Packing Units**

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.51 in (64.8 cm)
Package 1 Width	5.98 in (15.2 cm)
Package 1 Length	7.01 in (17.8 cm)
Package 1 Weight	6.44 lb(US) (2.92 kg)

#### **Contractual warranty**

Warranty

2 years repair or replace

Life Is On by Schneider Electric

## Sustainability

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



Energy Efficient Take-back Transparency RoHS/REACh

#### **Resource performance**

Energy Efficient Product

Take-Back Program Available

#### Well-being performance

Lead Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

