

# Product data sheet

Specifications



## UPS Network Management Card 2 w/ Environmental Monitoring, Out of Band Access and Modbus

AP9635

### Overview

Lead time Usually in Stock

### Main

Provided Equipment CD with software  
Temperature Sensor  
User Manual

### Physical

Height 1.50 in (3.81 cm)

Width 4.76 in (12.1 cm)

Depth 4.25 in (10.8 cm)

Net Weight 0.31 lb(US) (0.14 kg)

Mounting preference No preference

Mounting Mode Not rack-mountable

### Conformance

Standards EN 55022 Class A  
FCC Part 15 class A  
ICES-003

Product Certifications AS/NZS 3548 (C-Tick) Class A  
GOST  
VCCI Class A

### Environmental

Ambient Air Temperature for Operation 23...113 °F (-5...45 °C)

Operating altitude 0...10000 ft

Relative Humidity 0...95 % non-condensing

Ambient Air Temperature for Storage 5...149 °F (-15...65 °C)

Storage altitude 0...50000 ft (0.00...15240.00 m)

Storage Relative Humidity 0...95 %

### Communications & Management

Authentication Radius

## Ordering and shipping details

---

GTIN 731304267768

## Packing Units

---

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.01 in (5.1 cm)
Package 1 Width	6.26 in (15.9 cm)
Package 1 Length	9.25 in (23.5 cm)
Package 1 Weight	2.01 lb(US) (0.91 kg)

## Offer Sustainability

---

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

---

Warranty 2 years repair or replace

## Recommended replacement(s)