

# Product data sheet

Specifications



## Extension Cable for use w/ UPS communications cable 15'/5m

AP9815

### Overview

Lead time Usually in Stock

### Main

Cable length 15 ft (4.57 m)

Number of cables 1

Product Compatibility UPS

### Physical

Color Gray

Net Weight 0.99 lb(US) (0.45 kg)

Mounting Location Front

Mounting Mode Not rack-mountable

Connector B SUB-D 9 male Serial Straight Through

Connector A SUB-D 9 female Serial Straight Through

### Environmental

Storage Relative Humidity 0...95 %

Storage altitude 0...50000 ft (0.00...15240.00 m)

Ambient Air Temperature for Operation 32...113 °F (0...45 °C)

Relative Humidity 0...95 %

Operating altitude 0...10000 ft

Ambient Air Temperature for Storage 5...113 °F (-15...45 °C)

### Ordering and shipping details

GTIN 731304002727

### Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

<b>Package 1 Height</b>	9.02 in (22.9 cm)
<b>Package 1 Width</b>	2.01 in (5.1 cm)
<b>Package 1 Length</b>	4.02 in (10.2 cm)
<b>Package 1 Weight</b>	0.99 lb(US) (0.45 kg)

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>California proposition 65</b>	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
<b>Optimized Energy Efficiency</b>	Energy efficient product
<b>Take-back</b>	Take-back program available

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Recommended replacement(s)