



APC Back-UPS Pro 500VA, Lithium Ion UPS

BG500

- ! Discontinued on: Dec 31, 2019
- ! End-of-service on: Nov 12, 2022

(!) Discontinued

Overview

Lead Time Special Order - Call for Quoted Lead Times

Main

mam	
Main Input Voltage	120 V
Kw Rating	300 W
Rated Power In Va	500 VA
Output Connection Type	4 NEMA 5-15R
Cable Length	6 ft (1.83 m)
Number Of Cables	1
Battery Type	Li-lon (Lithium Ion)

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Included Battery Modules	0
Battery Slots Empty	0
Typical Recharge Time	16 h
Rbc Quantity	1
Battery Charge Power (Watts)	2 W rated
Battery Life	58 year(s)
Extendable Run Time	0

General

Provided Equipment	Cat 5 ethernet cable CD with software Installation guide Telephone Cable User Manual USB cable Wall-mounting template Warranty card
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Color	Black
Height	2.13 in (5.4 cm)
Width	11.42 in (29 cm)
Depth	7.52 in (19.1 cm)
Net Weight	4.85 lb(US) (2.2 kg)
Mounting Support	Desktop Wall
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Vertical Horizontal

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Switching Current Capacity	7 A

Output

Max Configurable Power (Watts)	300 W
Output Frequency (Sync To Mains)	50/60 Hz +/- 3 Hz sync to mains
Topology	Standby
Wave Type	Quasi-sine Wave
Graph Start Point	10
Maximum Configurable Power In Va	500 VA
Transfer Time	8ms typical : 10 ms maximum

Conformance

Product Certifications	California (CEC) Battery Charger cTUVus
Equipment Protection Policy	Lifatima : \$150000

Environmental

Ambient Air Temperature For Operation	50104 °F (1040 °C)
Relative Humidity	1090 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	5113 °F (-1545 °C)
Storage Relative Humidity	1090 %
Storage Altitude	050000 ft (0.0015240.00 m)
Acoustic Level	45 dBA

Communications & Management

Surge Protection and Filtering

Surge Energy Rating

613 J

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
Gtin	731304299585
Returnability	No
Country Of Origin	PH

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.82 in (9.7 cm)
Package 1 Width	11.18 in (28.4 cm)
Package 1 Length	14.57 in (37 cm)
Package 1 Weight	6.39 lb(US) (2.9 kg)
Scc14	10731304299582
Pallet Unit Layers	24
Pallet Layers	3

Contractual warranty

Warranty

Apr 27, 2024

3 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information