

Product data sheet

Specifications



APC Back-UPS Pro, 1350VA/810W, Tower, 120V, 10x NEMA 5-15R outlets, Sine Wave, AVR, USB Type A + C ports, LCD, User Replaceable Battery

BR1350MS

Product availability : Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main


Main Input Voltage	120 V
Kw Rating	810 W
Rated power in VA	1350 VA
Output connection type	6 NEMA 5-15R 4 NEMA 5-15R surge
Cable length	6 ft (1.83 m)
Number of cables	1
Battery Type	Lead-Acid battery

General

Provided equipment	Coaxial cable User Manual USB cable
Product web sub-family	Gaming performance
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Height	10.24 in (26 cm)
Width	3.94 in (10 cm)
Depth	14.49 in (36.8 cm)
Net Weight	25.79 lb(US) (11.7 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Two post mountable	0
USB compatible	No
Input	
Input Frequency	60 Hz +/- 3 Hz
Efficiency at full load	88...147 V
Maximum Input Current per Phase	12 A
Switching current capacity	15 A
Output	
Max Configurable Power (Watts)	810 W
Output frequency	60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Maximum configurable power in VA	1350 VA
Transfer Time	8ms typical : 10 ms maximum
Conformance	
Product Certifications	ENERGY STAR V2.0 (USA) NOM TUV C-US certified
Equipment protection policy	Lifetime : \$500000
Environmental	
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...10000 ft (0.00...3048.00 m)
Acoustic level	45 dBA
Batteries & Runtime	
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
RBC Quantity	2
Battery Charge Power (Watts)	10 W rated
Battery power in VAH	168 VAh capacity 168 VAh runtime
Battery Life	3...5 year(s)
Replacement battery	APCRBC161 
Extendable Run Time	0

Communications & Management

Control panel Multi-function LCD status and control console

Surge Protection and Filtering

Surge energy rating 1080 J

Filtering Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in

Ordering and shipping details

Category 11309-APC RESALE PRODUCTS

Discount Schedule APC1

GTIN 00731304335399

Returnability No

Country of origin PH

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 14.12 in (35.87 cm)

Package 1 Width 18.98 in (48.2 cm)

Package 1 Length 8.78 in (22.3 cm)

Package 1 Weight 29.32 lb(US) (13.3 kg)

SCC14 10731304335396

Offer Sustainability

California proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

ENERGY STAR® [ENERGY STAR UPS V2.0 \(USA\)](#) [↗](#)

REACH Regulation [REACH Declaration](#)

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Mercury free Yes

RoHS exemption information [Yes](#)

Optimized Energy Efficiency Energy efficient product

Take-back Take-back program available

Contractual warranty

Warranty 3 years repair or replace

Recommended replacement(s)