

Product data sheet

Specifications



APC Back-UPS Pro External Battery Pack (for 1500VA Back-UPS Pro models, formerly Back-UPS RS 1500)

BR24BPG

Product availability : Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Number of cables 1
Battery Type Lead-Acid battery
Provided Equipment User Manual

Physical

Color Black
Height 11.85 in (30.1 cm)
Width 4.41 in (11.2 cm)
Depth 15.04 in (38.2 cm)
Net Weight 29.54 lb(US) (13.4 kg)
USB compatible No

Conformance

Product Certifications TÜV

Environmental

Relative Humidity 0...95 %
Storage Relative Humidity 0...95 %
Ambient Air Temperature for Storage 5...113 °F (-15...45 °C)
Ambient Air Temperature for Operation 32...104 °F (0...40 °C)
Operating altitude 0...30000 ft
Storage altitude 0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Device mounting Stand alone battery stack

Battery Life	4...6 year(s)
Battery Voltage	24 V
Battery Capacity	18 Ah
Included Battery Modules	2
Battery Slots Empty	0
RBC Quantity	1
Battery power in VAh	372 VAh

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304268789
Returnability	No

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	15.75 in (40 cm)
Package 1 Width	9.45 in (24 cm)
Package 1 Length	19.33 in (49.1 cm)
Package 1 Weight	32.12 lb(US) (14.569 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Height	53.15 in (135 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	770.86 lb(US) (349.656 kg)
SCC14	10731304268786

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Recommended replacement(s)