

Product data sheet

Specifications



APC AV J Type 1.5kVA Power Conditioner with Battery Backup & AVR 120V

J35B

! Discontinued on: 06 December 2021

! Discontinued

J35B has not been replaced. Please contact your customer care center for more information.

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	865 W
Rated power in VA	1500 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R 2 NEMA 5-15R surge
Battery Type	Lead-Acid battery
Provided equipment	CD with software User Manual

Physical

Color	Black
Height	3.84 in (9.76 cm)
Width	17.00 in (43.18 cm)
Depth	16.00 in (40.64 cm)
Net Weight	30.86 lb(US) (14 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Output

Max Configurable Power (Watts)	865 W
Waveform Type	Stepped approximation to a sine wave

Conformance

Standards	FCC Part 15 class B UL 1778
Equipment protection policy	Lifetime : \$350000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...10000 ft (0.00...3048.00 m)
Acoustic level	45 dBA

Batteries & Runtime

Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h

Surge Protection and Filtering

Surge energy rating	345 J
---------------------	-------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304277699
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	8.07 in (20.51 cm)
Package 1 width	22.00 in (55.88 cm)
Package 1 Length	21.24 in (53.94 cm)
SCC14	10731304277696
Number of Units in Package 2	2
Package 2 Weight	74.93 lb(US) (33.99 kg)
Package 2 Height	17 in (431.80 mm)
Package 2 width	23 in (584.20 mm)
Package 2 Length	22 in (558.80 mm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	3 years repair or replace
-----------------	---------------------------
