

Product data sheet

Specifications



APC Performance SurgeArrest 12 Outlet with 2 Port 2.4 A USB Charger 120V

P12U2

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	6 ft (1.83 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Black
Height	12.24 in (31.1 cm)
Width	5.00 in (12.7 cm)
Depth	1.30 in (3.3 cm)
Net Weight	1.92 lb(US) (0.87 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Switching current capacity	15 A

Output

Number of power socket outlets	12
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	L-N: 330 L-G: 400 N-G: 400
---------------------	----------------------------------

Product Certifications	cULus
------------------------	-------

Standards	FCC Part 15 class B
-----------	---------------------

UL 1310
UL 1363
UL 1449

Equipment protection policy Lifetime : \$300000

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	75 dB
Peak current	56 kA common mode 196 kA normal mode
Surge energy rating	4320 J

Ordering and shipping details

GTIN	731304336563
Package weight(Lbs)	2.16 lb(US) (0.98 kg)

Packing Units

Package 1 Height	14.17 in (36 cm)
Package 1 width	7.87 in (20 cm)
Package 1 Length	1.69 in (4.3 cm)
SCC14	10731304336560
Number of Units in Package 2	6
Package 2 Weight	14.4 lb(US) (6.53 kg)
Package 2 Height	8.98 in (228.09 mm)
Package 2 width	11.42 in (290.07 mm)
Package 2 Length	15.16 in (385.06 mm)
Number of Units in Package 3	216

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty

Limited Lifetime