

# Product data sheet

Specifications



## APC Notebook Surge Protector for AC, phone and network lines, 3 pin connection, 100-240V

PNOTEPROC6

**Product availability : Stock - Normally stocked in distribution facility**

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	120 V
Input Connection Type	IEC 60320 C6
Number of cables	1
Provided equipment	2 x 1.8 Meter Tel cable 30 cm Network patch cable Cord management straps User Manual

### Physical

Color	Silver
Height	1.10 in (2.8 cm)
Width	1.26 in (3.2 cm)
Depth	4.33 in (11 cm)
Net Weight	0.22 lb(US) (0.1 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Input power	300 W
Maximum Line Current per phase	4 A
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	1
Outlet standard	IEC 60320 C6

### Conformance

UL 1449 TVSS Rating	700
Product Certifications	CSA

NOM  
UL Listed

**Standards** FCC part 68

**Equipment protection policy** Lifetime : \$75000

## Environmental

**Ambient air temperature for operation** 32...104 °F (0...40 °C)

**Relative Humidity** 0...95 %

**Operating altitude** 0...10000 ft

**Ambient Air Temperature for Storage** 5...113 °F (-15...45 °C)

**Storage Relative Humidity** 0...95 %

**Storage altitude** 0...30000 ft (0.00...9144.00 m)

## Surge Protection and Filtering

**NM Surge Response Time (ns)** 1 ns common mode

**Common mode rejection** 0 dB

**Peak current** 12 kA common mode  
6.5 kA normal mode

**Surge energy rating** 600 J

**Data Line Protection** RJ11 Modem/Fax protection (two wire single line)  
RJ45 10/100 Base-T Ethernet protection

## Ordering and shipping details

**Category** 11309-APC RESALE PRODUCTS

**Discount Schedule** APC1

**GTIN** 731304220701

**Returnability** No

## Packing Units

**Unit Type of Package 1** PCE

**Number of Units in Package 1** 1

**Package 1 Height** 2.72 in (6.9 cm)

**Package 1 Width** 7.76 in (19.7 cm)

**Package 1 Length** 6.22 in (15.8 cm)

**Package 1 Weight** 0.44 lb(US) (0.2 kg)

**Number of Units in Package 2** 12

**Package 2 Height** 8.3 in (210.82 mm)

**Package 2 Width** 11.5 in (292.10 mm)

**Package 2 Length** 16.5 in (419.10 mm)

**Package 2 Weight** 6 lb(US) (2.72 kg)

**Number of Units in Package 3** 480

**SCC14** 10731304220708

## Offer Sustainability

**Sustainable offer status** Green Premium product

<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	Yes
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>Circularity Profile</b>	<a href="#">End of Life Information</a>

## Contractual warranty

<b>Warranty</b>	Limited Lifetime
-----------------	------------------

## Recommended replacement(s)