Product data sheet

Specifications





APC Smart-UPS, Line Interactive, 1500VA, Tower, 120V, 8x NEMA 5-15R outlets, Network Card, AVR, LCD

SMT1500NC

! Discontinued on: May 3, 2022

! End-of-service on: May 4, 2024

① Discontinued

Overview

Lead Time	Usually in Stock
Main	
Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	1000 W
Rated Power In Va	1440 VA
Input Connection Type	NEMA 5-15P
Output Connection Type	8 NEMA 5-15R
Cable Length	6 ft (1.83 m)
Number Of Cables	1
Battery Type	Lead-Acid battery
Provided Equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable USB cable

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical Recharge Time	3 h
Rbc Quantity	1
Battery Life	35 year(s)
Replacement Battery	RBC7 ☐
Battery Charge Power (Watts)	136 W rated

General



Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Physical

_	
Color	Black
Height	8.62 in (21.9 cm)
Width	6.73 in (17.1 cm)
Depth	17.28 in (43.9 cm)
Net Weight	53.20 lb(US) (24.13 kg)
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	Yes

Input

Efficiency At Full Load	75154 V adjustable 82144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic Distortion	Less than 5%
Maximum Configurable Power In Va	1440 VA
Max Configurable Power (Watts)	1000 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Wave Type	Sine wave
Output Frequency (Sync To Mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CSA
Equipment Protection Policy	Lifetime : \$150000

Environmental

Acoustic Level	45 dBA
Heat Dissipation	135 Btu/h
Operating Altitude	010000 ft
Ambient Air Temperature For Operation	32104 °F (040 °C)
Ambient Air Temperature For Storage	5113 °F (-1545 °C)
Storage Altitude	050000 ft (0.0015240.00 m)
Relative Humidity	095 %

Communications & Management

Control Panel	Multi-function LCD status and control console
Free Slots	0
Pre-Installed Smartslot™ Cards	Network management card 2 with environmental monitoring
Alarm	Alarm when on hattery: distinctive low hattery alarm: configurable delays

Surge Protection and Filtering

Surge Energy Rating	459 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Gtin	731304332749
Country Of Origin	PH

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.80 in (37.6 cm)
Package 1 Width	23.43 in (59.5 cm)
Package 1 Length	12.91 in (32.8 cm)
Package 1 Weight	60.10 lb(US) (27.26 kg)

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Learn more about Green Premium >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product



Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation

REACh Declaration

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov