

Product datasheet

Specifications



RACK PDU, BASIC, VERTICAL, 220-240V, 32A, (20) C13, (6) C19

AP6009A

Overview

Lead time Usually in Stock

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60309 32 A 2P + E
Number of rack unit	0U
Cable length	3.05 m
Number of cables	1
Provided equipment	Installation guide Safety guide

Physical

Height	162.6 cm
Width	5.6 cm
Depth	4.3 cm
Net weight	6.18 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Permissible voltage	200...240 V
Input current limits	32 A
Load capacity	7400 VA
Network frequency	50/60 Hz

Output

Number of power socket outlets	20 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Product certifications	CE EAC IRAM VDE
------------------------	--------------------------

Environmental

Ambient air temperature for operation	0...50 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	8 kg
Package 1 Height	187.5 cm
Package 1 Width	22.6 cm
Package 1 Length	13.5 cm
Number of Units in Package 3	35

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)