

# Product datasheet

Specifications



## RACK PDU, BASIC, 0U/1U, 120-240V/15A, 220-240V/10A, (8) C13

AP6015A

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage 100 V  
120 V  
200 V  
208 V  
230 V  
240 V

Main Output Voltage 100 V  
120 V  
200 V  
208 V  
230 V  
240 V

Input Connection Type IEC 60320 C14

Number of rack unit 1U

Provided equipment Installation guide  
Safety guide

### Physical

Colour Black

Height 24 cm

Width 4.4 cm

Depth 9.3 cm

Net weight 0.91 kg

Mounting location Front  
Rear

Mounting preference No preference

Mounting mode Not rack-mountable

### Input

[In] rated current 12 A

Permissible voltage 100...240 V

Max line current 15 A

Input current limits 15 A

---

Load capacity	2300 VA
Network frequency	50/60 Hz

---

## Output

---

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

---

## Conformance

---

Product certifications	cUL listed CE EAC IRAM UL listed VDE
------------------------	---

---

## Packing Units

---

Package 1 Weight	1.37 kg
Package 1 Height	28.6 cm
Package 1 width	21 cm
Package 1 Length	13 cm
SCC14	10731304327797
Number of Units in Package 3	192

---

## Offer Sustainability

---

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

---

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------

---