# **Product datasheet**

Specifications



## Rack PDU, Metered, Zero U, 10A, 230V, (16) C13

AP7850B

### **Overview**

Lead Time

Usually in Stock

#### Main

mann		
Colour	Black	
Pdu Type	Metered	
Cord Length	3.05 m	
Number Of Cables	1	
Provided Equipment	Cord retention bracket(s) Installation guide Rack mounting brackets Toolless mounting kit	

### Complementary

e emprementar y	
Input Voltage	200 V 208 V 230 V
Height	124.5 cm
Width	5.6 cm
Output Voltage	230 V
Depth	4.4 cm
Net Weight	3.07 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	0U
Mounting Position	Vertical
Permissible Voltage	200250 V
Max Line Current	10 A
Load Capacity	2300 VA
Network Frequency	4763 Hz
Total Number Of Outlets	16 IEC 60320 C13

## **Environment**



Product Certifications	CE GOST VDE
Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.4 cm
Package 1 Width	32.3 cm
Package 1 Length	38.7 cm
Package 1 Weight	3.98 kg

### **Contractual warranty**

Warranty

2 years repair or replace

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



Energy Efficient Take-back Transparency RoHS/REACh

#### **Resource performance**

Zenergy Efficient Product

Take-Back Program Available

#### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

