

Product datasheet

Specifications



Power Cord Kit (6 ea), Locking, C13 to C14 (90 Degree), 1.2m

AP8704R-WW

Overview

Presentation Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time Usually in Stock

Main

Input Connection Type IEC 60320 C14

Cable length 1.22 m

Number of cables 6

Provided equipment 3 left-angle jumper cords
3 right-angle jumper cords

Physical

Colour Black

Height 24 cm

Width 7 cm

Depth 4.5 cm

Net weight 1.01 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Max line current 10 A

Input current limits 10 A

Output

Max current draw 10 A

Number of power socket outlets 1 IEC 60320 C13

Power cable length 1.22 m

Conformance

Product certifications	CCC PSE VDE
------------------------	-------------------

Environmental

Ambient air temperature for operation	0...70 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	4.5 cm
Package 1 Length	7 cm
Package 1 Weight	1.01 kg
Number of Units in Package 3	390

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)