

# Product datasheet

Specifications



## Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, Red

AP8704S-WWX340

### Overview

Lead time Usually in Stock

### Main

Input Connection Type IEC 60320 C14

Cable length 1.22 m

Number of cables 6

### Physical

Colour Red

Height 24 cm

Width 7 cm

Depth 4.5 cm

Net weight 1.01 kg

Mounting preference No preference

Mounting mode Not rack-mountable

### Input

Max line current 10 A

Input current limits 10 A

### Output

Max current draw 10 A

Number of power socket outlets 1 IEC 60320 C13

Power cable length 1.22 m

### Conformance

Product certifications CCC  
PSE  
VDE

## Environmental

Ambient air temperature for operation	0...70 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0.00...15240.00 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	4.5 cm
Package 1 Length	7 cm
Package 1 Weight	1.01 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)