

Product datasheet

Specifications



Rack PDU, Basic, Zero U, 10A,230V, (15)C13



AP9568

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V 200 V 208 V 230 V 240 V
Main Output Voltage	208 V 230 V
Input Connection Type	IEC 60320 C14
Number of rack unit	0U
Cable length	1.98 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets Toolless mounting kit

Physical

Colour	Black
Height	61 cm
Width	4.4 cm
Depth	4.4 cm
Net weight	2 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Permissible voltage	100...240 V
Input current limits	10 A
Load capacity	2300 VA
Network frequency	50/60 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Number of power socket outlets 15 IEC 60320 C13

Conformance

Product certifications cUL listed
CE
GOST
Queensland Australia
UL listed
VDE

Environmental

Ambient air temperature for operation 0...45 °C

Relative humidity 0...95 %

Operating altitude 0...10000 ft

Ambient air temperature for storage -25...65 °C

Storage Relative Humidity 0...95 %

Storage altitude 0.00...15240.00 m

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 64.8 cm

Package 1 Width 17.8 cm

Package 1 Length 15.2 cm

Package 1 Weight 2.724 kg

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

EU RoHS Directive Compliant
[EU RoHS Declaration](#)

Lead free Yes

WEEE The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Optimized Energy Efficiency Energy efficient product

Take-back Take-back program available

Contractual warranty

Warranty 2 years repair or replace

Recommended replacement(s)