

Product datasheet

Specifications



APC Replacement Battery Cartridge #113 with 2 Year Warranty

APCRBC113

Overview

Lead time Usually in Stock

Main

Product or component type Replacement battery cartridge

Battery type Lead-acid battery

Provided equipment All required connectors
Battery recycling guide
Installation guide
Reusable packaging

Physical

Colour Black

Height 10.2 cm

Width 13.3 cm

Depth 15.2 cm

Net weight 6.8 kg

Mounting mode Not rack-mountable

Output

Battery capacity 7.0 Ah

Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 %

Ambient air temperature for storage -5...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

Batteries & Runtime

Number of battery free slots 0

Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Battery voltage	24 V
Number of battery replacement quantity	1
Replacement battery	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14 cm
Package 1 Width	17.1 cm
Package 1 Length	21 cm
Package 1 Weight	7 kg
SCC14	10731304260049

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)