

Product datasheet

Specifications



APC Replacement Battery Cartridge #142 with 2 Year Warranty

APCRBC142

Overview

Lead time Usually in Stock

Main

Battery type Lead-acid battery

Provided equipment All required connectors
Battery recycling guide
Installation guide
Reusable packaging

Physical

Height 10.8 cm

Width 13.2 cm

Depth 15 cm

Net weight 6.01 kg

Mounting mode Not rack-mountable

USB compatible No

Environmental

Ambient air temperature for operation 0...40 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 %

Ambient air temperature for storage -15...45 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

Batteries & Runtime

Number of battery blocks per string 2

Number of battery free slots 0

Number of battery filled slots 0

Device mounting Stand alone battery stack

Battery voltage	24 V
Number of battery replacement quantity	1

Packing Units

Package 1 Weight	7.01 kg
Package 1 Height	20.3 cm
Package 1 width	16.8 cm
Package 1 Length	22.4 cm
SCC14	10731304291975
Number of Units in Package 3	75

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------