
# **Product datasheet**

Specifications





# NetShelter 2 Post Rack 45U #12-24 Threaded Holes Black

AR201

## Overview

Lead Time

Usually in Stock

#### Main

Number Of Rack Unit	45U
Number Of Cables	1
Provided Equipment	24 x #12-24 x 0.5 inch pilot screws User manual

### **Physical**

Colour	Black
Height	213.6 cm
Width	51.3 cm
Depth	37.6 cm
Net Weight	11.82 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	104.8 cm
Rack Width	19"
Marking	3 gauge post
Permanent Permissible Load	340.19 kg static

#### Conformance

Product Certifications	UL listed TAA
Standards	EIA-310E

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	220 cm
Package 1 Length	16 cm



Package 1 Weight


#### **Contractual warranty**

Warranty

2 years repair or replace

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

