

Product datasheet

Specifications



APC Replacement Battery Cartridge, VRLA battery, 10Ah, 48VDC, 2-year warranty

RBC43

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Product Or Component Type	Replacement battery cartridge
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cartridge
Battery Voltage	48 V
Number Of Battery Replacement Quantity	1

Physical

Height	7.6 cm
Width	21.6 cm
Depth	53.3 cm
Net Weight	19.09 kg
Mounting Mode	Not rack-mountable
Usb Compatible	No

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.900 cm
Package 1 Width	76.800 cm
Package 1 Length	39.400 cm
Package 1 Weight	20.450 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	12
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	257.160 kg

Contractual warranty


Warranty	2 years repair or replace.
----------	----------------------------


Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)







Take-back

Transparency


RoHS/REACH

Resource performance



Take-Back Program Available

Well-being performance



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information