

Product datasheet

Specifications

APC SERVICE BYPASS PDU, 230V 10AMP W/ (6) IEC C13



SBP1500RMI

Overview

Lead time Usually in Stock

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C14
Number of rack unit	2U
Cable length	1.98 m
Number of cables	1
Provided equipment	User manual Rack mounting brackets

Physical

Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	7.6 cm
Net weight	2 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Network frequency	50/60 Hz
Permissible voltage	220...240 V
Max line current	10 A
Input current limits	10 A
Load capacity	1500 VA
Power factor	0...1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Max current draw	10 A
Number of power socket outlets	6 IEC 60320 C13 1 IEC Jumpers 6
Protection type	Circuit breaker
Power cable length	1.22 m
Efficiency	99 %

Conformance

Product certifications	VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Height	15.1 cm
Package 1 Width	46.3 cm
Package 1 Length	29.5 cm
Package 1 Weight	3.5 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	56
Package 2 Height	113 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	195.608 kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)