

Product datasheet

Specifications

APC SERVICE BYPASS PDU, 230V 16AMP Hardwire



SBP3000RMHW

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Output connector type	Hard wire 3-wire (H N + E) 1
Number of rack unit	2U
Provided equipment	User manual Rack mounting brackets

Physical

Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	7.6 cm
Net weight	2.27 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Network frequency	50/60 Hz
Permissible voltage	220...240 V
Max line current	16 A
Input current limits	16 A
Load capacity	3000 VA
Power factor	0...1

Output

Max current draw	16 A
Number of power socket outlets	1 IEC Jumpers

Protection type	Circuit breaker
Power cable length	1.00 m
Efficiency	99 %

Conformance

Product certifications	VDE
------------------------	-----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	3.45 kg
Package 1 Height	15.1 cm
Package 1 width	46.3 cm
Package 1 Length	29.5 cm
Number of Units in Package 3	56

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------