

Product datasheet

Specifications



APC Smart-UPS, Line Interactive, 1500VA, Rackmount 2U, 230V, 4x IEC C13 outlets, SmartConnect Port +SmartSlot, AVR, LCD

SMT1500RMI2UC

Overview

Presentation Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.

Lead time Usually in Stock

Main

Main Input Voltage 230 V

Other Input Voltage 220 V
240 V

Main Output Voltage 230 V

Other Output Voltage 220 V
240 V

Rated power in W 1000 W

Rated power in VA 1500 VA

Input Connection Type IEC 320 C14

Nb of power socket outlets 4 IEC 320 C13
2 IEC Jumpers C13

Number of rack unit 2U

Battery type Lead-acid battery

Provided equipment Installation guide
Rack mounting support rails
USB cable

General

Number of power module filled slots 0

Number of power module free slots 0

Product web sub-family Cloud-enabled monitoring

Redundant No

Physical

Colour Black

Height 8.6 cm

Width 43.2 cm

Depth	47.7 cm
Net weight	26.1 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	151...302 V adjustable 160...286 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1500 VA
Maximum configurable power in W	1000 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE EAC RCM TÜV VDE
------------------------	--------------------------------

Environmental

Acoustic level	46 dBA
Heat dissipation	90 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h

Number of battery replacement quantity	1
Battery life	3...5 year(s)
Battery power in VAH	432 VAh runtime
Battery charger power	144 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Optional
Free slots	1

Surge Protection and Filtering

Surge energy rate	459 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	31.91 kg
Package 1 Height	25.1 cm
Package 1 width	59.4 cm
Package 1 Length	60.3 cm
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---